

AGENTS.

FIRST FLOOR,
40 ST. GEORGE'S STREET,
CAPE TOWN.

SLIDE BULES



CHSTECK

"DARMSTADT"

1/54 Wood-based rule 1/54A Wood-based rule with Addiator calculator 111/54 Geroplast rule *) 111/54A Geroplast rule with Addiator calculator*)

*) with trigonometrical graduations on the face of the slide rule.

OCCUPATIONS:

Physicists. Technicians dealing with High Frequency. Mathematicians.
Scientific Workers. Electrical and Mechanical Engineers. Radio Engineers. Students.

FUNCTIONS:

B:

For multi-plication, division and calculation of ratios. Fixed basic araduation Movable basic graduation

Reciprocal scale: For simple and compound multiplication and division, in conjunction with D and C.

Fixed square graduation Movable square

For calcu-lating squares and square

graduation Cubic graduation: for calculating cubes and cube roots.

Logarithmic graduation: For calculating mantissae and characteristics.

Pythagorean scale: for calculating formula $y = \sqrt{1-x^2}$, in conjunction with scales C and D for vectorial calculations.

S, T: Trigonometrical graduations: for problems involving angles.

Inch graduation: can be used — in conjunction with the scale on the base of the rule — as gauge for measuring hollow spaces. Back of Slide:

Exponential graduation: 1.01 — 105: for calculating "e" functions and also of powers with whole and fractional exponents, also for the con-struction of hyperbolic functions.

Also available with 400d graduation

CHSTELL "RIETZ" 1/87 Wood-based rule

2

OCCUPATIONS: Mechanical Engineers.

Building Engineers. Mechanical Technicians. Draughtsmen. Works Managers. Students in Technical Schools.

FUNCTIONS:

C, D: Basic Graduations: for multiplication and division.

Reciprocal Scale: for simple and compound multiplica-tion and division, in conjunction with C and D.

A, B: Square Graduations: for calculating squares and square roots.


Cubic Graduation: for calculating cubes and cube roots.

Logarithmic Scale.

Inch graduation: can be used — in conjunction with the scale on the base of the rule - as gauge for measuring hollow spaces.

Back of Slide:

S,ST,T: Trigonometric graduations. Also available with 400d scale.



CHSTELL

"ELECTRO"

1/98 Wood-based rule
111/98 Geroplast rule *)

OCCUPATIONS:

Electrical Engineers.
Electrical Technicians.
Works Managers in the Electrical
Industry.
Electrical Engineering Trainees.
Electricians.


FUNCTIONS:

- C,D: Basic graduations: for multiplication and division.
- Cr: Reciprocal graduation: for simple and compound multiplication and division.
- A, B: Square graduations: for calculation of squares and square roots.
- LU,LL: Log-Log or exponential graduation from 1·1 to 100,000, for calculating powers with whole or fractional exponents, and also for constructing hyperbolic functions.
- W: Scale for determining efficiency of dynamos and motors.
- -V: Scale for determining voltage-drop in electric circuits.
- Cu: Cubic graduation: for calculation of cubes and cube roots.

Inch graduation.

Back of Slide:

- S: Sine-cosine graduation.
- L: Logarithmic graduation.
- T: Tan-cotan graduation.



*) with the scales W and V on the face of the slide rule

OCCUPATIONS:

Surveyors. Surveyors' Assistants. Geometricians. Cartographers.

FUNCTIONS:

- C, D: Basic graduations: for multiplication, division and calculation of ratios
- lation of ratios.
 -Cr: Reciprocal graduation: for simple and compound multi-
- plication and division.

 A, B: Square graduations: for calculation of squares and square roots.
- L: Logarithmic graduation.
- P: Pythagorean graduation: for problems involving the formula $y = \sqrt{1-x^2}$
- S,T: Sine-cosine and tan-cotan graduation.
- Inch graduation: can be used in conjunction with the scale on the base of the rule as gauge for measuring hollow spaces.

Back of Slide:

Sine-cosine graduation and cos²-graduation for determining difference in height and horizontal distance.

"BUSINESS" 1/22 Wood-based rule 1/22 A Wood-based rule with Addiator calculator 111/22 Geroplast rule *) 111/22 A Geroplast rule with Addiator calculator *)

#2-15-0, Nos 2/- pestagento

FUNCTIONS:

OCCUPATIONS:

Bankers and Financiers. Commercial Employees.

Businessmen.

Civil Servants.

D, C: Lower graduations of main body and slide: for multiplication, division and calculation of ratios.

- A, B: Upper graduations of main body and slide: complementary to D and C.

Cr: Central graduation of slide: for calculation of interest and for compound multiplication and division.

L: Logarithmic graduation.

Adjustment-marks for international variations in weights and measures.

Scale for conversion of s and d into decimals of English $\mathfrak E.$

- Inch graduation.

Back of Slide:

E: Exponential graduation for calculation of compound interest.

*) with the scale for conversion of s and d on the face of the rule

OCCUPATIONS:

Businessmen.
Dealers in Technical Apparatus.
Wholesalers and Retailers.
Economists.
Factory Technicians.

FUNCTIONS:

 D,C: Lower graduation of main body and slide: for multiplication, division and calculation of ratios.

- A, B: Upper graduation of main body and slide: complementary to D and C.

- Cr: Central graduation of slide: for calculation of interest and for compound multiplication and division.

-S: Square graduation.

- Cu: Cubic graduation.

L: Logarithmic graduation.

- Inch graduation.

-Scale for conversion of s and d into decimals of English £.

Back of Slide:

E: Exponential graduation for calculation of compound interest.

CHSTECC "MACHINE-TIME" 1/48 Wood-based rule

OCCUPATIONS:

Technicians in the Metal Industry. Works Engineers. Factory Technicians. Time Computers. Foremen.

FUNCTIONS:

Upper graduation of main body: For machine times and performances; also usable — in conjunction with lower graduation of main body for multiplication and division.

Upper graduation of slide: For operating-distance (machining-length). For working diameter or stroke. Lower graduation of slide: For

cutting-speed. For feed or belt-speed.

Lower graduation of main body: to be used in conjunction with back of slide for multiplying and dividing. Border Graduation:

For r.p.m. or double strokes per

minute. Inch graduation.


Back of Slide:

Upper graduation:

Square graduation: for calculation of squares and square roots.

Lower graduation:

Basic graduation: for multiplication and division; also for calculating weights.



OCCUPATIONS:

Mechanical Engineers. Mathematicians. Physicists. Scientific Workers.

FUNCTIONS:

C, D: Basic graduations: for multi-

plication and division. Reciprocal graduation: for simple and compound multiplication and division.

A, B: Square graduations: for calculation of squares and square roots.

LU,LL: Log-Log or exponential graduation from 1.1 to 100,000, for calculating powers with whole or fractional exponents, and also for constructing hyperbolic functions.


Cu: Cubic graduation: for calculations of cubes and cube roots.

Back of Slide:

Sine-cosine graduation.

Logarithmic graduation.

Tan-cotan graduation.



PROFESSIONS:

CHSTECC Physicists. "MATHEMA" work. 2/84*) Geroplast rule (FRONT) (g In Y) g tan Y (ln Y) FUNCTIONS: (BACK) -0,1 Yg tanh y g sinh y

PROFESSIONS:

Mathematicians.

Engineers engaged in scientific

FUNCTIONS:

Natural logarithm (in "new degrees").

Tangent and cotangent scales ("new degrees").

Hyperbolic scale (Pythagorean Scale II).

Parabolic Scales (quadratic scales).

Reciprocal Parabolic Scale (reciprocal quadratic scale).

Reciprocal Basic Scale (from 15-0.7).

Basic Scales (from 0.07-1.5).

Circular Scale (Pythagorean Scale I).

Sine and Cosine Scale ("new degrees").

Natural Logarithm.

*) English instructions in preparation

e 0,1Y e 10Y

Exponential Scales with negative exponents.

> Scale of hyperbolic tangent (in "new degrees").

g cosh 10y Scale of hyperbolic cosine (in "new degrees").


g sinh 10y 1st scale of hyperbolic sine (in "new degrees").

> 2nd scale of hyperbolic sine (in "new degrees").

Exponential Scales with positive

exponents.

Through a special vernier arrangement of the cursor the range of application for the natural logarithm scales is extended to 108. Special marks on the cursor enable readings to be taken immediately.



PROFESSIONS:

Engineers Technicians Businessmen The Textile industry

FUNCTIONS:

- cm-scale.

D: Fixed basic scale.

C: Movable basic scale.

BI: Reciprocal scale (in conjunction with A and B).

A: Fixed quadratic scale.

B: Movable quadratic scale.

A': Scale for conversion of Kgs. into English lbs. (454 g).

Z₁ Z₂ (Back of Slide) Z₃ (Back of Slide)

The individual scales and also the cursor have marks corresponding to the various factors for the conversion of yarn-sizes, thread-thicknesses, lengths and weights, etc.


*) in preparation





FABER-CASTELL Slide Rules


are the only ones in the world supplied in various models with the original Addiator calculator for additions and subtractions. The adding apparatus also shows debit-balances. Construction: with brass insertions and lateral steel spring base (wood based rules only);

as shown in the illustration (in the case of Geroplast rules).











CASTELL-Cursors

The CASTELL Slide-Rules are fitted with "open-view" cursors made of perspex (Fig. A). These give an absolutely unimpeded view of the entire system of graduations on the rule, the glass parts at the sides being constructed with the same object.



If specially required, these "open view" cursors will be supplied with semi-cylindrical lenses (Fig. B), giving increased accuracy in reading. With the three-and four-line cursors the semi-cylindrical lens is adjustable along the cursor, according to the particular cursor-line being used.



For especially exacting requirements where reading-accuracy is concerned, the slide-rules can be fitted with periscopic magnifying cursors (Fig. C). The magnifying glass is swivel-mounted so that the table of constants on the back of the slide-rule can be read with equal ease.

CASTELL Slide Rules of GEROPLAST

Geroplast is a special Faber-Castell material selected, for its excellent properties, from among the many different types of material available for the manufacture of Slide Rules.

Its outstanding feature is the "high fidelity" of the engraved graduations which retain their initial accuracy after many years of use. The Slide Rule shown in the illustration is made of Geroplast: note the "sharpness" of the graduation-marks and their perfect legibility. Geroplast is also impervious to climatic influences. Castell Geroplast Slide Rules are non-inflammable and can be recommended for use in laboratories.

Cleaning Medium for slide rules


No. 211	Liquid for cleaning slide rule facings	
No. 212	Paste for cleaning slide rule facings	

TABLE SHOWING THE OPERATIONS WHICH CAN BE CARRIED OUT WITH THE VARIOUS "CASTELL" MODELS.

		ling ab ole dire					lings obtainable with one movement of the slide. 1 factor. For 2 factors. For 3 factors						Further Fields of Calculation:		
"Business" 67/22	4					a·b, a			a·b·c		Interest, arbitrage, percentages, ratios, conversion of s and d into decimals of a				
"Business" 1/22 "Business" 4/22	ā	1 log a		+ -	,	√a	ė	` =	a	$\frac{1}{a^2}$, $\frac{1}{a^2}$			a b · c a · b c	As before, also compound interest, c version of foreign weights and meas	con-
"Super-Business" 1/28		α3, √α, √α3, √α2			-1%			وآو	a3.b3,61			U	04.b3, c3 b3.√c3	Simple and compound interes arbitrage.	it,
"Stadia" 1/38			sina, tga cosa, ctga			a 3 3/a,		, Va 1				, a ² .b ² .c	Š	Determining differences in height and also horizontal distances on open land.	2
"Darmstadt" 1/54 4/54 "Darmstadt" 67/54	, log a		42, Si					- g - g	a 3 · b 3,			a.b. √c		Functions n	Se
"Mathema" 2/84	المراقبة المراقبة المراقب المراقبة المراقبة المراقبة المراقبة المراقب المراقب المراقبة المراقب المراقب المراقبة المراقب المراقبة المراقبة المراقبة المراقب	a 2,5 a 1,6 a 1,25		ن ا ا	V1+a2	-1, 50		a Vb, 1		6, 6, 6,0	व विक	29. P2	. b3. V&	of e, such as e ⁿ , e ⁻ⁿ , \sqrt{e}	with triangles
"Duplex" 2/82	d 2,			-1.5				D		92.	· tg a	b2.c2	a 3 · b 3	also a 10 , $\sqrt{a_i}$ In a_i a n , $\sqrt{a_i}$	vith t
"Riety" 1/87 "Riety" 4/87 "Riety" 67/87		³ √α, √α ³ , √α ²	10	.0	۵۶,۵6		g a, ctg a ab², a²b², <mark>a²</mark>	a²b²,	1, 10, 10, 10, 10, 10, 10, 10, 10, 10, 1	$(a \cdot b) \sqrt{\frac{a}{b}} \cdot \frac{1}{\sqrt{a \cdot b}}$	sinα, α , b	a.b, a.b.c.	·b³·c³, ^{a¹·b³} ,	Calculation of angles below 5° 43'.	Calculations
"Electro" 1/98 "Electro" 4/98		0 3 V	-16	_	-13		cosα, fg	- ola	a³.b³,	۸	d s.	, c, b	о. С	Determining the efficiency of dynamos and motors also voltage-drop in circuits, cal-	S
"Electro" 67/98	-			_	1 a 4, a 5	α³, ³ √σ΄, √α³, ³ √α²	sinα,	a · b,				a.b		culation of ohmic resistance, calculation of weight of cop- per transmission-lines.	

These and all other types of "CASTELL" Slide-Rules are supplied with adequate instructions.

HOW THE SLIDE-RULES ARE CONSTRUCTED.



Layer of celluloid on which scale is marked.

Metal insert to stabilise shape and render slide-rule easier to operate.

Cursor-groove.

Resilient slide-rule base, with latticespring.

Layer of celluloid on which scale is marked.

Metal insert to stabilise shape and render slide-rule easier to operate.

Adjusting-screw for setting slide to desired degree of freedom of movement.

Resilient slide-rule base, with latticespring. The system of graduations engraved on the layer of celluloid by a special process is extremely regular and accurate besides being easily legible.

All CASTELL Slide-Rules constructed of wood have metal inserts in order to make their shape more stable. Rules which have become warped from unusual causes may therefore be bent back into their original position without undesirable consequences.

A lattice-spring extending over the entire length of the slide-rule enables it to be adjusted easily and accurately without detracting from the freedom of movement of the slide.

In the slide-rule with a graduated length of 20" the base-spring is also combined with adjusting-screws whereby tension can be applied, or removed, to ensure the slide running flush to the face of the stock scales. Despite the length of the rule, this adjustment assures an easy movement of the slide.